

**FAHRION®**  
FAHRENDEN PROTEKTION**ER collet, ER 25, Nominal clamping Ø d: 11 mm****Order data**

Order number	308941 11
GTIN	2050001765659
Item class	39Y

**Description****Version:**

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

**Advantage:**

The coating increases the service life of the collet and ensures full functionality and precision.

**Note:**

The **collet clamping Ø range is always up to 1 mm less than nominal**, e.g. Ø 10 – 9 mm, **except for Ø 1, 1.5 and 2 (where it is only 0.5 mm)**.

**Technical description**

Nominal clamping Ø d	11 mm
Adapter	ER 25
Standard	ISO 15488-B
Concentricity	≤ 5 µm
Type	430 E
External Ø D	26 mm
Overall length L	34 mm

Type of product

Collet