



ER collet HP, ER 25, Nominal clamping \varnothing d: 11 mm



Order data

| | |
|--------------|---------------|
| Order number | 309373 11 |
| GTIN | 2050001764645 |
| Item class | 39Y |

Description

Version:

System concentricity and repetition accuracy **3 μ m** ($3 \times D$, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for:

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

Technical description

| | |
|----------------------------------|----------------|
| Nominal clamping \varnothing d | 11 mm |
| Adapter | ER 25 |
| Standard | ISO 15488-B |
| Concentricity | $\leq 2 \mu$ m |
| Type | 430 E |

| | |
|------------------|--------|
| External Ø D | 26 mm |
| Overall length L | 34 mm |
| Type of product | Collet |