



## LED rechargeable work light, Type: 360



### Order data

Order number	081543 360
GTIN	4062406056858
Item class	02A

### Description

#### Version:

LED rechargeable work lamp with adjustable lamp head angle, rotary knob for stepless dimming. Translucent cover for non-dazzle 360° illumination. Stand with integral magnet and suspension hook.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with charging cable and plug-in power supply unit.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 60 - 1000 lm

Working life: 1.5 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Overall length: 260 mm

### Technical description

## Data sheet

IP Index of Protection	IP 54
Lamp replaceable	no
Battery voltage	3.7 V
Type of rechargeable battery	Lithium-ion
Illumination	60 - 1000 lm
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	1
Working life	1.5 h
Bulb	LED module
ATEX zone	no
Weight	470 g
Overall length	260 mm
Type of product	Work lamp