

**LED rechargeable work light, Type: 380****Order data**

Order number	081549 380
GTIN	4062406056865
Item class	02A

Description**Version:**

Slim LED rechargeable lamp with main beam and spotlight for illumination even in narrow spaces. Free-moving rotary knob for stepless dimming. Flexible attachment by means of rotary magnetic base with integral suspension hook.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Charging cable.

Technical description

Battery voltage	3.7 V
Number of rechargeable batteries contained	1
Illumination time	2.5 h
IP Index of Protection	IP 54

Illumination	120 - 500 lm
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Overall length	380 mm
ATEX zone	no
Weight	250 g
Type of product	Fluorescent lamp