

**LED rechargeable pen light, Type: 170****Order data**

| | |
|--------------|---------------|
| Order number | 081579 170 |
| GTIN | 4062406056872 |
| Item class | 02A |

Description**Version:**

LED rechargeable pen light with main beam and spotlight, with a pocket clip with powerful attachment magnet. Magnetic base with 360° rotation.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Including USB charging cable.

Technical description

| | |
|-------------------|--------|
| Illumination | 220 lm |
| Illumination time | 2.5 h |
| Battery voltage | 3.7 V |
| ATEX zone | no |
| Weight | 83 g |

| | |
|--|------------------------------|
| Battery capacity | 1.1 Ah |
| Bulb | LED module |
| Illumination step 2 | 80 lm |
| IP Index of Protection | IP 20 |
| Number of rechargeable batteries contained | 1 |
| Overall length | 170 mm |
| Type of rechargeable battery | Lithium-ion |
| Overall width | 20 mm |
| Power supply | Rechargeable battery-powered |
| Type of product | Flashlight |