

Garant**Tightening screw with internal cooling, for mandrel Ø: 22mm****Order data**

Order number	575096 22
GTIN	4062406057060
Item class	53D

Description**Version:**

Tightening screw (galvanised) with hex socket. **With through coolant holes.**

Application:

For clamping GARANT round and disc brushes. **Check the torque.**

Technical description

Head Ø	32 mm
recommended tightening torque	20 Nm
for mandrel Ø	22 mm
Width across flats	6 mm
Thread M	M10
Head thickness K	8.5 mm
Type of product	Tightening screw

