

FAHRION®
FAHRENDEN PRESSION
ER collet HP, ER 32, Nominal clamping Ø d: 14mm

Order data

Order number	309376 14
GTIN	2050001768254
Item class	39Y

Description
Version:

System concentricity and repetition accuracy **3 µm** (3×D, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for:

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

Technical description

Nominal clamping Ø d	14 mm
Adapter	ER 32
Standard	ISO 15488-B
Concentricity	≤ 2 µm
Type	470 E

External Ø D	33 mm
Overall length L	40 mm
Type of product	Collet