



## ER collet HP, ER 11, Nominal clamping $\varnothing$ d: 1mm



### Order data

Order number	309368 1
GTIN	2050001766144
Item class	39Y

### Description

#### Version:

**System concentricity** and repetition accuracy **3  $\mu$ m** ( $3 \times D$ , maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

#### Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

#### Suitable for:

Precision ER collet chuck CENTRO P.

#### Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

### Technical description

Nominal clamping $\varnothing$ d	1 mm
Adapter	ER 11
Standard	ISO 15488-B
Concentricity	$\leq 2 \mu$ m
Type	4008 E

External $\varnothing$ D	11.5 mm
Overall length L	18 mm
Type of product	Collet