

FAHRION®
FAHREYOND PRECISION
ER collet HP with seal, ER 11, Nominal clamping Ø d: 5mm

Order data

Order number	309369 5
GTIN	2050001765734
Item class	33F

Description
Version:

System concentricity and repetition accuracy **3 µm** (3×D, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for:

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

With **seal** for through-coolant feed (for use up to 60 bar). **Similar to** ISO 15488-A.

Technical description

Nominal clamping Ø d	5 mm
Adapter	ER 11
Standard	ISO 15488-A
Concentricity	≤ 2 µm
Type	4012 E

External \varnothing D	11.2 mm
Overall length L	18 mm
Type of product	Collet