

FAHRION®
FAHRENDEN PROTEKTION**ER collet, ER 25, Nominal clamping Ø d: 13mm****Order data**

Order number	308941 13
GTIN	2050001766472
Item class	39Y

Description**Version:**

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

The **collet clamping Ø range is always up to 1 mm less than nominal**, e.g. Ø 10 – 9 mm, **except for Ø 1, 1.5 and 2 (where it is only 0.5 mm)**.

Technical description

Nominal clamping Ø d	13 mm
Adapter	ER 25
Standard	ISO 15488-B
Concentricity	≤ 5 µm
Type	430 E
External Ø D	26 mm
Overall length L	34 mm

Type of product

Collet