

**FAHRION®**  
FAHRENDEN PRESSION
**ER collet HP, ER 25, Nominal clamping  $\varnothing$  d: 7mm**

**Order data**

Order number	309373 7
GTIN	2050001768384
Item class	39Y

**Description**
**Version:**

**System concentricity** and repetition accuracy **3  $\mu$ m** ( $3 \times D$ , maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

**Advantage:**

The coating increases the service life of the collet and ensures full functionality and precision.

**Suitable for:**

Precision ER collet chuck CENTRO P.

**Note:**

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

**Technical description**

Nominal clamping $\varnothing$ d	7 mm
Adapter	ER 25
Standard	ISO 15488-B
Concentricity	$\leq 2 \mu$ m
Type	430 E

External $\varnothing$ D	26 mm
Overall length L	34 mm
Type of product	Collet