



## ER collet HP with seal, ER 32, Nominal clamping $\varnothing$ d: 4mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 309377 4      |
| GTIN         | 2050001767271 |
| Item class   | 33F           |

### Description

#### Version:

**System concentricity** and repetition accuracy **3  $\mu$ m** ( $3 \times D$ , maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

#### Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

#### Suitable for:

Precision ER collet chuck CENTRO P.

#### Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

With **seal** for through-coolant feed (for use up to 60 bar). **Similar to** ISO 15488-A.

### Technical description

|                                  |                |
|----------------------------------|----------------|
| Nominal clamping $\varnothing$ d | 4 mm           |
| Adapter                          | ER 32          |
| Standard                         | ISO 15488-A    |
| Concentricity                    | $\leq 2 \mu$ m |
| Type                             | 469 E          |

|                  |         |
|------------------|---------|
| External Ø D     | 32.7 mm |
| Overall length L | 40 mm   |
| Type of product  | Collet  |