

FAHRION®
FAHRENDEN PRESSION
ER collet HP, ER 40, Nominal clamping Ø d: 4mm

Order data

| | |
|--------------|---------------|
| Order number | 309379 4 |
| GTIN | 2050001768414 |
| Item class | 39Y |

Description
Version:

System concentricity and repetition accuracy **3 µm** (3×D, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for:

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

Technical description

| | |
|----------------------|-------------|
| Nominal clamping Ø d | 4 mm |
| Adapter | ER 40 |
| Standard | ISO 15488-B |
| Concentricity | ≤ 2 µm |
| Type | 472 E |

| | |
|------------------|--------|
| External Ø D | 41 mm |
| Overall length L | 46 mm |
| Type of product | Collet |