

**ER collet for machine taps with seal, ER 20, Nominal clamping \varnothing d: 10mm****Order data**

Order number	309406 10
GTIN	2050001768063
Item class	39Y

Description**Version:**

With square socket drive for positive engagement of the tap.
With sealing plugs for through coolant supply (up to 60 bar!).

FAHRION® corrosion protection:

- Collet completely coated, including the mating faces.
- This increases the service life of the collet and ensures full functionality and precision.

Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

Note:

FAHRION® collets similar to ISO 15488-A.

Technical description

Nominal clamping \varnothing d	10 mm
Adapter	ER 20
Standard	ISO 15488-A
Concentricity	$\leq 10 \mu\text{m}$
Type	4276 E
External \varnothing D	20.7 mm

Overall length L	31.5 mm
Type of product	Collet