



## ER collet for machine taps with seal, ER 40, Nominal clamping $\varnothing$ d: 20mm



### Order data

Order number	309419 20
GTIN	2050001765451
Item class	39Y

### Description

#### Version:

With square socket drive for positive engagement of the tap.  
With sealing plugs for through coolant supply (up to 100 bar!).

#### FAHRION® corrosion protection:

- Collet completely coated, including the mating faces.
- This increases the service life of the collet and ensures full functionality and precision.

#### Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

#### Note:

FAHRION® collets similar to ISO 15488-A.

### Technical description

Nominal clamping $\varnothing$ d	20 mm
Adapter	ER 40
Standard	ISO 15488-A
Concentricity	$\leq 10 \mu\text{m}$
Type	4716 E
External $\varnothing$ D	40.7 mm

Overall length L	46 mm
Type of product	Collet