

FAHRION®
FAHRION® PRESSION**ER collet for machine taps with seal, ER 25, Nominal clamping Ø d: 7mm****Order data**

Order number	309409 7
GTIN	2050001766892
Item class	39Y

Description**Version:**

With square socket drive for positive engagement of the tap.
With sealing plugs for through coolant supply (up to 60 bar!).

FAHRION® corrosion protection:

- Collet completely coated, including the mating faces.
- This increases the service life of the collet and ensures full functionality and precision.

Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

Note:

FAHRION® collets similar to ISO 15488-A.

Technical description

Nominal clamping Ø d	7 mm
Adapter	ER 25
Standard	ISO 15488-A
Concentricity	≤ 10 µm
Type	4282 E
External Ø D	25.7 mm

Overall length L	34 mm
Type of product	Collet