



ER collet for machine taps with seal and spray nozzles, ER 25, Nominal clamping \varnothing d: 8mm



Order data

Order number	309413 8
GTIN	2050001765802
Item class	39Y

Description

Version:

With square socket drive for positive engagement of the tap.

With sealing plugs for through coolant supply (up to 60 bar!) and spray nozzles.

FAHRION® corrosion protection:

- Collet completely coated, including the mating faces.
- This increases the service life of the collet and ensures full functionality and precision.

Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

Note:

FAHRION® collets similar to ISO 15488-A.

Technical description

Nominal clamping \varnothing d	8 mm
Adapter	ER 25
Standard	ISO 15488-A
Concentricity	$\leq 10 \mu\text{m}$
Type	4282 E

External Ø D	25.7 mm
Overall length L	34 mm
Type of product	Collet