



ER collet for machine taps with seal, ER 20, Nominal clamping \varnothing d: 9mm



Order data

| | |
|--------------|---------------|
| Order number | 309406 9 |
| GTIN | 2050001765864 |
| Item class | 39Y |

Description

Version:

With square socket drive for positive engagement of the tap.
With sealing plugs for through coolant supply (up to 60 bar!).

FAHRION® corrosion protection:

- Collet completely coated, including the mating faces.
- This increases the service life of the collet and ensures full functionality and precision.

Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

Note:

FAHRION® collets similar to ISO 15488-A.

Technical description

| | |
|----------------------------------|-----------------------|
| Nominal clamping \varnothing d | 9 mm |
| Adapter | ER 20 |
| Standard | ISO 15488-A |
| Concentricity | $\leq 10 \mu\text{m}$ |
| Type | 4276 E |
| External \varnothing D | 20.7 mm |

| | |
|------------------|---------|
| Overall length L | 31.5 mm |
| Type of product | Collet |