

FAHRION®
FAHRENDEN PRESSION
ER collet for machine taps with seal, ER 32, Nominal clamping \varnothing d: 7mm

Order data

Order number	309414 7
GTIN	2050001765895
Item class	39Y

Description
Version:

With square socket drive for positive engagement of the tap.

With sealing plugs for through coolant supply (up to 60 bar!).

FAHRION® corrosion protection:

- **Collet completely coated, including the mating faces.**
- **This increases the service life of the collet and ensures full functionality and precision.**

Suitable for:

All standard ER collet chucks, FAHRION collets also for the Centro P precision ER collet chuck.

Note:

FAHRION® collets similar to ISO 15488-A.

Technical description

Nominal clamping \varnothing d	7 mm
Adapter	ER 32
Standard	ISO 15488-A
Concentricity	$\leq 10 \mu\text{m}$
Type	4537 E
External \varnothing D	32.7 mm

Overall length L	40 mm
Type of product	Collet