

**ER collet, ER 8, Nominal clamping  $\varnothing$  d: 4,5mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 308878 4,5    |
| GTIN         | 2050001767035 |
| Item class   | 39Y           |

**Description****Version:**

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces.

**Advantage:**

The coating increases the service life of the collet and ensures full functionality and precision.

**Note:**

The **collet clamping  $\varnothing$  range is always up to 1 mm less than nominal**, e.g.  $\varnothing$  10 – 9 mm, **except for  $\varnothing$  1, 1.5 and 2 (where it is only 0.5 mm).**

**Technical description**

|                                  |                      |
|----------------------------------|----------------------|
| Nominal clamping $\varnothing$ d | 4.5 mm               |
| Adapter                          | ER 8                 |
| Standard                         | ISO 15488-B          |
| Concentricity                    | $\leq 5 \mu\text{m}$ |
| Type                             | 4004 E               |
| External $\varnothing$ D         | 8.5 mm               |
| Overall length L                 | 13.6 mm              |

Type of product

Collet