

FAHRION®
PRAZISION
ER collet set HP with seal (4; 6; 8; 10; 12; 14; 16; 20mm), 469 E, ER 32

Order data

Order number	309397
GTIN	2050001766441
Item class	33F

Description
Version:

System concentricity and repetition accuracy **3 µm** (3×D, maximum = 50 mm), in conjunction with FAHRION CENTRO P chucks.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Suitable for :

Precision ER collet chuck CENTRO P.

Note:

- **Optimum concentricity only when used in CENTRO P chucks.**
- **Clamping range h10 (nominal size only).**

Concentricity: $\leq 2 \mu\text{m}$

Technical description

Adapter	ER 32
Standard	ISO 15488-A
Concentricity	$\leq 2 \mu\text{m}$
Type of product	Clamping head

