

**Digital external micrometer set, Measuring range: 0-100mm****Order data**

Order number	421495 0-100
GTIN	4045197702210
Item class	42B

Description**Version:**

Easy-to-read display. Carbide-tipped anvils.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

External micrometers No. 421490 with appropriate micrometer standards.

Calibration: S2

IP Index of Protection: IP 54

Number of micrometers: 4

Number of micrometer standards: 3

Technical description

Measuring range	0 - 100 mm
Number of micrometers	4
Number of micrometer standards	3
Article no of the battery / rechargeable battery fitted	081560 357

Number of batteries contained	4
IP Index of Protection	IP 54
Power supply	Battery-powered
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Calibration	S2
Type of product	External micrometer

Services

Calibration External micrometer set Measuring range 0-100 mm	011070 0-100
Labelling laser-etched Type	018940
Calibration External micrometer set Measuring range 0-100 mm	020430 0-100

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------