



Digital external micrometer, Measuring range: 25-50mm



Order data

Order number	421490 25-50
GTIN	4045197701886
Item class	42B

Description

Version:

Easy-to-read display. Carbide-tipped anvils.

Digital and analogue graduations. Dust-proof and splash-proof metal casing.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357. 1 plug-in sphere for measuring curved surfaces.

From size 25–50, 1 micrometer standard.

Packaging: sturdy box

IP Index of Protection: IP 54

Calibration: B2

Calibration: B1

Scale divisions: 0.001 mm

Error limit: 4 µm

Spindle Ø: 6.5 mm

Spindle pitch: 0.5 mm

Technical description

Spindle Ø	6.5 mm
Spindle pitch	0.5 mm
Measuring range	25 - 50 mm

Error limit	4 µm
Scale divisions	0.001 mm
Calibration	B2
Calibration	B1
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 54
Power supply	Battery-powered
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration Micrometer standard for external micrometer maximum nominal size 100 mm	012110 100
Calibration External tube micrometer maximum measuring range 100 mm	012050 100
Labelling laser-etched Type	018940
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
100	022090 100
Calibration External tube micrometer maximum measuring range 100 mm	022000 100
Calibration Micrometer standard for external micrometer maximum nominal size 100 mm	022080 100
DAkkS calibration External micrometer maximum measuring range 100 mm	022010 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25
--------------------------------------------------	-----------

Button cell / special battery Battery type 357

081560 357