

Garant

Shrink fit chuck extension 3°, vibration-damped, L = 300 mm, Ø d / Ø D1: 25/10 mm



Order data

Order number	302417 25/10
GTIN	4045197701909
Item class	31P

Description

Version:

Shank bored through for internal coolant supply (ICS) up to maximum 80 bar. Including length adjustment backstop screw. A **carbide core embedded** in the adapter damps the tendency to vibrate.

Maximum permissible speed 8,000 rpm.

Advantage:

- **Avoid vibrations in the clamping system.**
- **Better workpiece surface finishes.**
- **Increased tool service lives.**

Vibration: damped

Ø D₂: 16 mm

Technical description

Shank Ø d	25 mm
Ø D ₂	16 mm
Bore Ø D ₁	10 mm
Overall length L	300 mm
Product name attribute	L = 300 mm
Through-coolant	yes, with max. 80 bar
Vibration	damped
Type of product	Shrink fit chuck accessories

