

**Garant****Swivel work chair, fabric cushion, with glides and footrest ring, high****Order data**

Order number	965042
GTIN	4045197702166
Item class	91Z

**Description****Version:**

Ergonomic swivel work chair with **synchro-technology**.

The soft mesh **fabric** of the seat and backrest is **comfortable** and **breathable**. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

**Standard:**

**DIN 68877**

**Note:**

The breathable mesh fabric is damaged by hook and loop fastenings. Please cover hook and loop fastenings.

**Technical description**

Lumbar support	yes
----------------	-----

Standard	DIN 68877
Seat depth adjustment range	40 mm
Material of seat surface	Mesh fabric
Backrest height	600 mm
Support frame version	5-point star base
Colour of seat material	black
Safe working load	120 kg
Synchro mechanism	yes
Backrest adjustment range	60 mm
Seat width	470 mm
Material of base	Aluminium matt powder coated
Base version	Glides with footrest ring
Seat depth	450 mm
Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Armrest pair can be adjusted	yes
Continuous contact backrest adjustment	yes
Version	high seat height
Load capacity chair	120 kg
Height adjustment range	640 - 890 mm
Type of product	Swivel work chair

## Accessories

Glides(1 set = 5 pieces)	962518
Pair of multi-function arm rests for the GARANT swivel work chair Type	965047