

Garant**Swivel work chair, integral foam, with castors, low****Order data**

Order number	965030
GTIN	4045197702111
Item class	91Z

Description**Version:**

Ergonomic swivel work chair with **synchro-technology**.

The soft **integral foam** of the seat and backrest is easy-care, washable, **robust** and resistant to weak acids and alkalis as well as mechanical impacts.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Standard:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**
- **Seat and backrest of soft integral foam.**
- **Easy-care, washable, robust and resistant to weak acids as well as mechanical impacts.**

Standard:

DIN 68877

Load capacity chair: 120 kg
 Height adjustment range: 480 - 630 mm
 Seat width: 470 mm
 Seat depth: 450 mm
 Backrest height: 600 mm
 Backrest height adjustment range: 60 mm
 Seat depth adjustment range: 40 mm
 Colour of seat material: black

Technical description

resistant to a limited extent against weak acids and alkalis	yes
Seat depth adjustment range	40 mm
Material of base	Aluminium matt powder coated
Support frame version	5-point star base
Roller version	Load-responsive castor braking for hard floors.
Safe working load	120 kg
Seat tilt adjustment	yes
Base version	Set of castors
Material of backrest	Integral foam
Lumbar support (spinal discs)	yes
Seat depth	450 mm
Backrest height adjustment range	60 mm
stepless height adjustment	yes
Standard	DIN 68877
Continuous contact backrest adjustment	yes
Seat width	470 mm
Synchro mechanism	yes
Armrest pair can be adjusted	yes
Material of seat surface	Integral foam
Backrest height	600 mm
Colour of seat material	black

Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Version	with castors
Load capacity chair	120 kg
Height adjustment range	480 - 630 mm
Type of product	Swivel work chair

Accessories

Spare castors (1 set = 5 pieces)	962517
Pair of multi-function arm rests for the GARANT swivel work chair	965047