

**Garant****Materials supply trolley, Height: 1700mm****Order data**

Order number	918590 1700
GTIN	4062406057251
Item class	91P

**Description****Version:**

**Frame and structure** of rectangular steel hollow section with sheet metal base. Insertion slots in the front and back of the frame (at 50 mm intervals) for fitting size 1000 mm shelves, multi-function rails etc. **Threaded sockets** on the inside of the frame for fitting perforated panels. 4 castors (2 with parking brakes, Ø **125mm**) with treadless polyurethane tyres, roller bearing hubs and a large push handle with Haptoprene® cover ensures safe handling.

**Application:**

Can be equipped with storage shelves, storage container racks, drawing display stands, Multifix rail, cross rail and perforated panels in size 1000.

**Colour:**

RAL 7035 light grey **powder-coated**.

**Technical description**

Weight	35 kg
Width	1100 mm
Height	1700 mm

Width without handle	1000 mm
Number of castors with parking brake	2
Suspension interval	50 mm
Number of castors without parking brake	2
Usable height	1370 mm
Wheel Ø	125 mm
Material of wheels	Treadless polyurethane tyres
Depth	700 mm
maximum load capacity	200 kg
Usable width	920 mm
Design version	Steel hollow section construction
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Materials supply trolley

## Accessories

Multifix suitable for type 1000	928201 1000
Perforated panel double-sided suitable for type 1000	928071 1000
Shelf with steel hoops suitable for type 1000	928145 1000
Cross rail suitable for usable width 920 mm	918603 920
Viewing window suitable for type 1000	928091 1000
Push handle Colour BLACK	920135 BLACK
Push handle Colour BLUE	920135 BLUE
Multifix rail open storage bins Length mm / Type 1000/AA1	928230 1000/AA1
Storage shelf of sheet metal 300 mm deep suitable for type 1000	928131 1000
Storage shelf of sheet metal 200 mm deep suitable for type 1000	928130 1000

Perforated panel single-sided suitable for type 1000	928070 1000
Drawing holder with organisation magnets suitable for type 1000	928211 1000
Additional hook Usable length 75 mm	918604 75
Multifix rail open storage bins Length mm / Type 1000/AB1	928230 1000/AB1
Additional hook Usable length 150 mm	918604 150
Shelf 610 mm deep suitable for usable width 920 mm	918592 920
Viewing window suitable for type 1000	928090 1000