

**Garant****Swivel work chair, fabric cushion, with glides, low****Order data**

Order number	965041
GTIN	4045197613462
Item class	91Z

**Description****Version:**

Ergonomic swivel work chair with **synchro-technology**.

The soft mesh **fabric** of the seat and backrest is **comfortable** and **breathable**. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

**Version of the advertising text:**

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

**Standard:**

**DIN 68877**

**Note:**

The breathable mesh fabric is damaged by hook and loop fastenings. Please cover hook and loop fastenings.

## Technical description

Material of seat surface	Mesh fabric
Base version	Glides
Seat depth	450 mm
Backrest adjustment range	60 mm
Material of base	Aluminium matt powder coated
Support frame version	5-point star base
Seat depth adjustment range	40 mm
Synchro mechanism	yes
Lumbar support	yes
Colour of seat material	black
Seat width	470 mm
Safe working load	120 kg
Standard	DIN 68877
Backrest height	600 mm
Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Armrest pair can be adjusted	yes
Continuous contact backrest adjustment	yes
Version	without castors
Load capacity chair	120 kg
Height adjustment range	490 - 630 mm
Type of product	Swivel work chair

## Accessories

Pair of multi-function arm rests for the GARANT swivel  
work chair Type

965047

Glides(1 set = 5 pieces)

962518