

Garant**Swivel work chair, integral foam, with glides, low****Order data**

Order number	965031
GTIN	4045197702128
Item class	91Z

Description**Version:**

Ergonomic swivel work chair with **synchro-technology**.

The soft **integral foam** of the seat and backrest is easy-care, washable, **robust** and resistant to weak acids and alkalis as well as mechanical impacts. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment: 40 mm.

Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Version of the advertising text:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**

Standard:

DIN 68877

Technical description

Safe working load	120 kg
Base version	Glides
Standard	DIN 68877
Lumbar support (spinal discs)	yes
Material of base	Aluminium matt powder coated
Seat tilt adjustment	yes
resistant to a limited extent against weak acids and alkalis	yes
Material of seat surface	Integral foam
Continuous contact backrest adjustment	yes
Synchro mechanism	yes
Backrest height	600 mm
stepless height adjustment	yes
Colour of seat material	black
Material of backrest	Integral foam
Armrest pair can be adjusted	yes
Backrest height adjustment range	60 mm
Seat depth adjustment range	40 mm
Seat depth	450 mm
Seat width	470 mm
Support frame version	5-point star base
Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Version	without castors
Load capacity chair	120 kg
Height adjustment range	490 - 630 mm
Type of product	Swivel work chair

Accessories

Glides(1 set = 5 pieces)

962518

Pair of multi-function arm rests for the GARANT swivel
work chair Type

965047