

Garant**Swivel work chair, fabric cushion, with castors, low****Order data**

Order number	965040
GTIN	4045197702142
Item class	91Z

Description**Version:**

Ergonomic swivel work chair with **synchro-technology**.

The soft mesh **fabric** of the seat and backrest is **comfortable** and **breathable**. Five-star aluminium base.

Seat (width×depth): 470×450 mm.

Backrest height: 600 mm.

Backrest adjustment range: 60 mm.

Seat depth adjustment range: 40 mm Load capacity: 120 kg.

High and narrow backrest allows freedom of movement for the arms.

Braked dual castors with soft PU treads.

Version of the advertising text:

- **Functional ergonomic design.**
- **Lumbar support.**
- **Synchronous technology.**
- **High and narrow backrest allows freedom of movement for the arms.**
- **Five-star aluminium base.**
- **Seat and backrest with soft mesh material.**
- **Comfortable and breathable.**

Standard:

DIN 68877**Note:**

The breathable mesh fabric is damaged by hook and loop fastenings. Please cover hook and loop fastenings.

Technical description

Seat depth adjustment range	40 mm
Base version	Set of castors
Material of base	Aluminium matt powder coated
Backrest adjustment range	60 mm
Roller version	Load-responsive castor braking for hard floors.
Colour of seat material	black
Material of seat surface	Mesh fabric
Synchro mechanism	yes
Lumbar support	yes
Safe working load	120 kg
Backrest height	600 mm
Support frame version	5-point star base
Standard	DIN 68877
Seat width	470 mm
Seat depth	450 mm
Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Armrest pair can be adjusted	yes
Continuous contact backrest adjustment	yes
Version	with castors
Load capacity chair	120 kg
Height adjustment range	480 - 630 mm
Type of product	Swivel work chair

Accessories

Pair of multi-function arm rests for the GARANT swivel work chair Type

965047

Spare castors(1 set = 5 pieces)

962517