



## Digital clinometer CLINOBEVEL 1 USB, Type:



### Order data

Order number	467555
GTIN	7630041115321
Item class	45C

### Description

#### Version:

Clinometer for universal use for absolute and relative measurements. Four precision-machined measurement bases permit inclination measurements in any designed quadrant. Strengthened housing of hard-anodised aluminium, protected against splashed water. With angular and inclination display.

#### Supplied with:

Incl. case.

Packaging: Wallet

IP Index of Protection: IP 65

Interface: USB interface

Measuring range:  $\pm 45$  degrees

Graduations: 0.02 mm/m

Accuracy: 2 +1 graduation arcmin

Length: 100 mm

Width: 75 mm

Height: 35 mm

### Technical description

Width	75 mm
-------	-------

Height	35 mm
Measuring range	±45 degrees
Length	100 mm
Accuracy	2 +1 graduation arcmin
Weight	520 g
Graduations	0.02 mm/m
IP Index of Protection	IP 65
Interface	USB interface
Power supply	Battery-powered
Standard	DIN 2276
Measurement technology	digital
Packaging	Wallet
Type of product	Clinometer