

Garant
RC.T 0602, Grade: HU7310-1


Order data

Order number	260620 HU7310-1
GTIN	4062406058388
Item class	21G

Description

RC.T 0602 HU7310-1 Chip breaker: AM
 Tolerance: G
 Cutting depth a_p : 0.5 - 2 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 350 - 600 m/min

Technical description

Cutting conditions	continuous
Cutting depth a_p	0.5 - 2 mm
Grade	HU7310-1
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Main application	N

Chip breaker	AM
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	RCGT 0602
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning