

Garant**RC.X 1204, Grade: HU7310-1**

Order data

Order number	260650 HU7310-1
GTIN	4062406058616
Item class	21G

Description

RC.X 1204 HU7310-1 Chip breaker: AM
Tolerance: G
Cutting depth a_p : 0.5 - 2 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 350 - 600 m/min

Technical description

Main application	N
Cutting depth a_p	0.5 - 2 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Chip breaker	AM
Tool material	Carbide
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 m/min

Cutting conditions	continuous
Grade	HU7310-1
Coating	uncoated
ISO code indexable insert	RCGX 1204
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning