

**Garant**
**RC.T 0803, Grade: HU7310-1**


### Order data

Order number	260630 HU7310-1
GTIN	4062406058395
Item class	21G

### Description

RC.T 0803 HU7310-1 Chip breaker: AM  
 Tolerance: G  
 Cutting depth  $a_p$ : 0.5 - 2 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 350 - 600 m/min

### Technical description

Tool material	Carbide
Chip breaker	AM
Cutting depth $a_p$	0.5 - 2 mm
Cutting speed $v_c$ main application	350 - 600 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting conditions	continuous
Feed $f$	0.1 - 0.3 mm/rev.

Grade	HU7310-1
Main application	N
Coating	uncoated
ISO code indexable insert	RCGT 0803
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning