




Jobber drill set HSS No. 114000 as refill set, uncoated, Type: 2-10



Order data

Order number	115020 2-10
GTIN	4045197024145
Item class	12B

Description

Version:

Composed of jobber drills DIN 338.

Through-coolant: no

Shank: Plain shank

Drill range: 2 - 10 mm

Number of drills: 81

Incremental steps of drills: 0.1 mm

Technical description

Number of drills	81
Drill range	2 - 10 mm
Incremental steps of drills	0.1 mm
Shank	Plain shank
Number of cutting edges Z	2
Coating	uncoated
Tool material	HSS
Type	N
Tolerance nominal \varnothing	h8
Point angle	118°
Through-coolant	no

with case	no
Colour ring	without
Type of product	Jobber drill

Accessories

HSS jobber drill roll forged N Ø DC h8 9,6 mm	114000 9,6
HSS jobber drill roll forged N Ø DC h8 6,7 mm	114000 6,7
HSS jobber drill roll forged N Ø DC h8 7,5 mm	114000 7,5
HSS jobber drill roll forged N Ø DC h8 3,8 mm	114000 3,8
HSS jobber drill roll forged N Ø DC h8 2,4 mm	114000 2,4
HSS jobber drill roll forged N Ø DC h8 2,6 mm	114000 2,6
HSS jobber drill roll forged N Ø DC h8 3,9 mm	114000 3,9
HSS jobber drill roll forged N Ø DC h8 6 mm	114000 6
HSS jobber drill roll forged N Ø DC h8 6,8 mm	114000 6,8
HSS jobber drill roll forged N Ø DC h8 7,3 mm	114000 7,3
HSS jobber drill roll forged N Ø DC h8 8 mm	114000 8
HSS jobber drill roll forged N Ø DC h8 2,8 mm	114000 2,8
HSS jobber drill roll forged N Ø DC h8 7,2 mm	114000 7,2
HSS jobber drill roll forged N Ø DC h8 4,9 mm	114000 4,9
HSS jobber drill roll forged N Ø DC h8 9,9 mm	114000 9,9
HSS jobber drill roll forged N Ø DC h8 6,4 mm	114000 6,4
HSS jobber drill roll forged N Ø DC h8 7,4 mm	114000 7,4
HSS jobber drill roll forged N Ø DC h8 9,4 mm	114000 9,4
HSS jobber drill roll forged N Ø DC h8 6,5 mm	114000 6,5
HSS jobber drill roll forged N Ø DC h8 8,2 mm	114000 8,2
HSS jobber drill roll forged N Ø DC h8 5,4 mm	114000 5,4
HSS jobber drill roll forged N Ø DC h8 4,1 mm	114000 4,1
HSS jobber drill roll forged N Ø DC h8 9 mm	114000 9

HSS jobber drill roll forged N Ø DC h8 4,2 mm	114000 4,2
HSS jobber drill roll forged N Ø DC h8 7,1 mm	114000 7,1
HSS jobber drill roll forged N Ø DC h8 4,7 mm	114000 4,7
HSS jobber drill roll forged N Ø DC h8 3,2 mm	114000 3,2
HSS jobber drill roll forged N Ø DC h8 9,8 mm	114000 9,8
HSS jobber drill roll forged N Ø DC h8 8,9 mm	114000 8,9
HSS jobber drill roll forged N Ø DC h8 9,7 mm	114000 9,7
HSS jobber drill roll forged N Ø DC h8 8,3 mm	114000 8,3
HSS jobber drill roll forged N Ø DC h8 3 mm	114000 3
HSS jobber drill roll forged N Ø DC h8 8,8 mm	114000 8,8
HSS jobber drill roll forged N Ø DC h8 5,1 mm	114000 5,1
HSS jobber drill roll forged N Ø DC h8 7,8 mm	114000 7,8
HSS jobber drill roll forged N Ø DC h8 4,5 mm	114000 4,5
HSS jobber drill roll forged N Ø DC h8 9,1 mm	114000 9,1
HSS jobber drill roll forged N Ø DC h8 4,6 mm	114000 4,6
HSS jobber drill roll forged N Ø DC h8 7,9 mm	114000 7,9
HSS jobber drill roll forged N Ø DC h8 6,9 mm	114000 6,9
HSS jobber drill roll forged N Ø DC h8 3,1 mm	114000 3,1
HSS jobber drill roll forged N Ø DC h8 3,3 mm	114000 3,3
HSS jobber drill roll forged N Ø DC h8 5,9 mm	114000 5,9
HSS jobber drill roll forged N Ø DC h8 3,6 mm	114000 3,6
HSS jobber drill roll forged N Ø DC h8 2,1 mm	114000 2,1
HSS jobber drill roll forged N Ø DC h8 6,1 mm	114000 6,1
HSS jobber drill roll forged N Ø DC h8 4,4 mm	114000 4,4
HSS jobber drill roll forged N Ø DC h8 2,3 mm	114000 2,3
HSS jobber drill roll forged N Ø DC h8 5,2 mm	114000 5,2
HSS jobber drill roll forged N Ø DC h8 3,4 mm	114000 3,4
HSS jobber drill roll forged N Ø DC h8 5,6 mm	114000 5,6
HSS jobber drill roll forged N Ø DC h8 2,5 mm	114000 2,5

HSS jobber drill roll forged N Ø DC h8 6,2 mm	114000 6,2
HSS jobber drill roll forged N Ø DC h8 3,7 mm	114000 3,7
HSS jobber drill roll forged N Ø DC h8 6,3 mm	114000 6,3
HSS jobber drill roll forged N Ø DC h8 8,5 mm	114000 8,5
HSS jobber drill roll forged N Ø DC h8 3,5 mm	114000 3,5
HSS jobber drill roll forged N Ø DC h8 5,3 mm	114000 5,3
HSS jobber drill roll forged N Ø DC h8 8,4 mm	114000 8,4
HSS jobber drill roll forged N Ø DC h8 8,1 mm	114000 8,1
HSS jobber drill roll forged N Ø DC h8 5,5 mm	114000 5,5
HSS jobber drill roll forged N Ø DC h8 5 mm	114000 5
HSS jobber drill roll forged N Ø DC h8 9,5 mm	114000 9,5
HSS jobber drill roll forged N Ø DC h8 4,8 mm	114000 4,8
HSS jobber drill roll forged N Ø DC h8 2,2 mm	114000 2,2
HSS jobber drill roll forged N Ø DC h8 5,8 mm	114000 5,8
HSS jobber drill roll forged N Ø DC h8 5,7 mm	114000 5,7
HSS jobber drill roll forged N Ø DC h8 9,3 mm	114000 9,3
HSS jobber drill roll forged N Ø DC h8 4,3 mm	114000 4,3
HSS jobber drill roll forged N Ø DC h8 10 mm	114000 10
HSS jobber drill roll forged N Ø DC h8 2 mm	114000 2
HSS jobber drill roll forged N Ø DC h8 7 mm	114000 7
HSS jobber drill roll forged N Ø DC h8 7,7 mm	114000 7,7
HSS jobber drill roll forged N Ø DC h8 7,6 mm	114000 7,6
HSS jobber drill roll forged N Ø DC h8 2,9 mm	114000 2,9
HSS jobber drill roll forged N Ø DC h8 2,7 mm	114000 2,7
HSS jobber drill roll forged N Ø DC h8 8,7 mm	114000 8,7
HSS jobber drill roll forged N Ø DC h8 6,6 mm	114000 6,6
HSS jobber drill roll forged N Ø DC h8 9,2 mm	114000 9,2
HSS jobber drill roll forged N Ø DC h8 4 mm	114000 4
HSS jobber drill roll forged N Ø DC h8 8,6 mm	114000 8,6