



Precision circlip pliers, Type: A0



Order data

Order number	719890 A0
GTIN	4003773048718
Item class	73F

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring**. **Form A – straight jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

Shape	A
for external circlips \varnothing	3 - 10 mm
overall length	140 mm
Tip \varnothing	0.9 mm
Standard	DIN 5254 A

Use of circlip pliers	Outer ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers