

Garant**Screw-on toolholder, right-hand, Shank / insert size: 16/06mm****Order data**

Order number	260606 16/06
GTIN	4062406059392
Item class	21T

Technical description

Insert size	6 mm
suitable indexable insert	RC.T 0602
Shank size	16 mm
Overall length L	100 mm
Head length L ₁	13.6 mm
Functional width L ₄	20 mm
Pack of insert screws	269028 22
ISO code toolholder	SRGCR/L 1616H06
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
