

Garant**Screw-on toolholder, right-hand, Shank / insert size: 20/06mm****Order data**

Order number	260606 20/06
GTIN	4062406059408
Item class	21T

Technical description

Overall length L	125 mm
Head length L ₁	15.3 mm
suitable indexable insert	RC.T 0602
Shank size	20 mm
Functional width L ₄	25 mm
Insert size	6 mm
Pack of insert screws	269028 22
ISO code toolholder	SRGCR/L 2020K06
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
