

Garant
Screw-on toolholder, left-hand, Shank / insert size: 12/06mm

Order data

Order number	260607 12/06
GTIN	4062406059453
Item class	21T

Technical description

Shank size	12 mm
Series	QuickTurn
Pack of insert screws	269028 22
Insert size	6 mm
Overall length L	80 mm
Functional width L ₄	16 mm
Head length L ₁	13.6 mm
ISO code toolholder	SRGCR/L 1212F06
suitable indexable insert	RC.T 0602
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500