

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 20/06mm**

**Order data**

Order number	260607 20/06
GTIN	4062406059477
Item class	21T

**Technical description**

Shank size	20 mm
Insert size	6 mm
Overall length L	125 mm
ISO code toolholder	SRGCR/L 2020K06
Functional width L <sub>4</sub>	25 mm
Series	QuickTurn
Head length L <sub>1</sub>	15.3 mm
Pack of insert screws	269028 22
suitable indexable insert	RC.T 0602
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500