




Electrician's screwdriver set for slot-head fully insulated, Number of screwdrivers: 6



Order data

Order number	663311 6
GTIN	4062406059750
Item class	62F

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.**

Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Multi-component power handle with grip zone optimised for torque and comfort. Blade of high-alloy tool steel. From size 5.5 the outside \varnothing of the insulation is the same as the tip width (helpful when working in narrow spaces).

Blades with taper tips, manufactured to the standard dimensions of slots on the screws. Fully insulated, the breakdown strength of the insulation is many times the minimum test voltage set by VDE. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Application:

For use at voltages up to 1000 V.

Optimum working life for electrician's screwdrivers is assured if screwdrivers always exactly match the standard screw slot size. (see tables part). Incorrect screwdriver size selection will cause damage to the screw head.

Content:

1 each screwdriver No. 663301: Size 2.5; 3; 3.5; 4; 5.5; 6.5

Technical description

Number of screwdrivers	6
------------------------	---

Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Slot-head screwdriver
Type of product	Screwdrivers

Accessories

Electrician's screwdriver for slot-headfully insulated Blade width b 2,5 mm	663301 2,5
Electrician's screwdriver for slot-headfully insulated Blade width b 3 mm	663301 3
Electrician's screwdriver for slot-headfully insulated Blade width b 4 mm	663301 4
Electrician's screwdriver for slot-headfully insulated Blade width b 6,5 mm	663301 6,5
Electrician's screwdriver for slot-headfully insulated Blade width b 3,5 mm	663301 3,5
Electrician's screwdriver for slot-headfully insulated Blade width b 5,5 mm	663301 5,5