

Garant GRIDLINE

## Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 400/2



### Order data

Order number	930505 400/2
GTIN	4062406060077
Item class	9GK

### Description

#### Version:

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

#### Fitted with:

Drawer front height, mm: 150, 150

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

### Technical description

Usable height for drawers	300 mm
Drawer usable width	500 mm
Width	600 mm

Drawer usable depth in G	20
Depth	600 mm
Number of doors	0
Weight	43 kg
Electronic locking system can be retrofitted	yes
Drawer usable depth	500 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer usable width in G	20
Height	400 mm
Drawer usable area in G	20×20
Number of drawers	2
Usable height	300 mm
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Tool cabinet

## Accessories

Drawer,75 kg Drawer front height 150 mm	930533 150
---	------------

Handle end caps 20 pieces Type 10	951025 10
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 400 mm	930525 400