

Garant GRIDLINE

## Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 800/7A



### Order data

Order number	930505 800/7A
GTIN	4062406066376
Item class	9GK

### Description

#### NOTE: Colour selection possible

#### Version:

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

#### Fitted with:

Drawer front height, mm: 50, 75, 75, 100, 100, 150, 150

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 20×20

Height: 800 mm

Width: 600 mm

Depth: 600 mm

Usable height: 700 mm  
 Usable height for drawers: 700 mm  
 Drawer usable width: 500 mm

## Technical description

Height	800 mm
Usable height for drawers	700 mm
Usable height	700 mm
Number of doors	0
Drawer usable area in G	20×20
Drawer usable width	500 mm
Number of drawers	7
Width	600 mm
Drawer usable width in G	20
Electronic locking system can be retrofitted	yes
Drawer usable depth in G	20
Drawer usable depth	500 mm
Weight	99 kg
Depth	600 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	150 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg

Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Tool cabinet

## Accessories

Drawer, 75 kg Drawer front height 150 mm	930533 150
Tool cabinet casing for drawers Height 800 mm	930525 800
Handle end caps 20 pieces Type 10	951025 10
Drawer, 75 kg Drawer front height 75 mm	930533 75
Lock plate for GridLine Type HU21	914227 HU21
Drawer, 75 kg Drawer front height 50 mm	930533 50
Drawer, 75 kg Drawer front height 100 mm	930533 100