

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 800/5**Order data**

Order number	930505 800/5
GTIN	4062406066338
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 75, 75, 150, 150, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer usable area in G	20×20
Height	800 mm

Number of doors	0
Drawer usable depth in G	20
Number of drawers	5
Width	600 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	250 mm
Drawer usable width	500 mm
Drawer usable width in G	20
Weight	86 kg
Usable height	700 mm
Usable height for drawers	700 mm
Electronic locking system can be retrofitted	yes
Drawer usable depth	500 mm
Depth	600 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Tool cabinet

Accessories

Drawer,75 kg Drawer front height 250 mm	930533 250
Drawer,75 kg Drawer front height 150 mm	930533 150
Tool cabinet casing for drawers Height 800 mm	930525 800
Drawer,75 kg Drawer front height 75 mm	930533 75
Lock plate for GridLine Type HU21	914227 HU21
Handle end caps20 pieces Type 10	951025 10