

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 800/7



Order data

Order number	930505 800/7
GTIN	4062406066369
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 100, 125, 150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 20×20

Height: 800 mm

Width: 600 mm

Depth: 600 mm

Usable height: 700 mm
 Usable height for drawers: 700 mm
 Drawer usable width: 500 mm

Technical description

Drawer usable width	500 mm
Width	600 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	150 mm
Weight	100 kg
Number of drawers	7
Drawer usable depth	500 mm
Drawer usable depth in G	20
Drawer usable width in G	20
Usable height	700 mm
Number of doors	0
Electronic locking system can be retrofitted	yes
Height	800 mm
Drawer usable area in G	20×20
Usable height for drawers	700 mm
Depth	600 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg

Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Tool cabinet

Accessories

Drawer, 75 kg Drawer front height 150 mm	930533 150
Handle end caps 20 pieces Type 10	951025 10
Drawer, 75 kg Drawer front height 75 mm	930533 75
Drawer, 75 kg Drawer front height 50 mm	930533 50
Lock plate for GridLine Type HU21	914227 HU21
Drawer, 75 kg Drawer front height 100 mm	930533 100
Tool cabinet casing for drawers Height 800 mm	930525 800
Drawer, 75 kg Drawer front height 125 mm	930533 125