

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 800/6**Order data**

Order number	930505 800/6
GTIN	4062406066345
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 125, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes

Drawer usable width	500 mm
Usable height for drawers	700 mm
Drawer usable depth in G	20
Depth	600 mm
Weight	93 kg
Number of doors	0
Number of drawers	6
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	250 mm
Drawer usable area in G	20×20
Height	800 mm
Usable height	700 mm
Drawer usable width in G	20
Width	600 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Tool cabinet

Accessories

Drawer,75 kg Drawer front height 250 mm	930533 250
Lock plate for GridLine Type HU21	914227 HU21
Drawer,75 kg Drawer front height 75 mm	930533 75
Drawer,75 kg Drawer front height 125 mm	930533 125
Handle end caps20 pieces Type 10	951025 10
Tool cabinet casing for drawers Height 800 mm	930525 800
Drawer,75 kg Drawer front height 50 mm	930533 50
Drawer,75 kg Drawer front height 100 mm	930533 100