

Garant GRIDLINE

**Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 400/3****Order data**

Order number	930505 400/3
GTIN	4062406066321
Item class	9GK

**Description****Version:**

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

**Fitted with:**

Drawer front height, mm: 100, 100, 100

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

Width	600 mm
Usable height for drawers	300 mm
Height	400 mm

Depth	600 mm
Drawer usable width	500 mm
Drawer usable depth	500 mm
Weight	51 kg
Number of doors	0
Usable height	300 mm
Electronic locking system can be retrofitted	yes
Drawer usable area in G	20×20
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Number of drawers	3
Drawer usable depth in G	20
Drawer usable width in G	20
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Tool cabinet

## Accessories

Tool cabinet casing for drawers Height 400 mm	930525 400
Handle end caps 20 pieces Type 10	951025 10
Lock plate for GridLine Type HU21	914227 HU21
Drawer, 75 kg Drawer front height 100 mm	930533 100