

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 900/10



Order data

Order number	930505 900/10
GTIN	4062406066406
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 50, 75, 75, 75, 75, 100, 100, 100, 100

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 20×20

Height: 900 mm

Width: 600 mm

Depth: 600 mm

Usable height: 800 mm
 Usable height for drawers: 800 mm
 Drawer usable width: 500 mm

Technical description

Usable height for drawers	800 mm
Drawer usable width	500 mm
Depth	600 mm
Drawer usable depth	500 mm
Number of doors	0
Drawer front height	50 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Weight	126 kg
Drawer usable area in G	20×20
Electronic locking system can be retrofitted	yes
Height	900 mm
Usable height	800 mm
Number of drawers	10
Drawer usable depth in G	20
Width	600 mm
Drawer usable width in G	20
Base cabinet underneath height-adjustable workstation	no

Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Tool cabinet

Accessories

Tool cabinet casing for drawers Height 900 mm	930525 900
Drawer, 75 kg Drawer front height 50 mm	930533 50
Handle end caps 20 pieces Type 10	951025 10
Drawer, 75 kg Drawer front height 75 mm	930533 75
Drawer, 75 kg Drawer front height 100 mm	930533 100
Lock plate for GridLine Type HU21	914227 HU21