

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 900/7A



Order data

| | |
|--------------|---------------|
| Order number | 930505 900/7A |
| GTIN | 4062406066390 |
| Item class | 9GK |

Description

NOTE: Colour selection possible

Version:

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 75, 75, 100, 100, 150, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 20×20

Height: 900 mm

Width: 600 mm

Depth: 600 mm

Usable height: 800 mm
 Usable height for drawers: 800 mm
 Drawer usable width: 500 mm

Technical description

| | |
|---|--------|
| Number of drawers | 7 |
| Height | 900 mm |
| Drawer usable depth in G | 20 |
| Depth | 600 mm |
| Electronic locking system can be retrofitted | yes |
| Weight | 105 kg |
| Drawer usable width in G | 20 |
| Drawer usable width | 500 mm |
| Usable height | 800 mm |
| Number of doors | 0 |
| Drawer front height | 50 mm |
| Drawer front height | 75 mm |
| Drawer front height | 75 mm |
| Drawer front height | 100 mm |
| Drawer front height | 100 mm |
| Drawer front height | 150 mm |
| Drawer front height | 250 mm |
| Usable height for drawers | 800 mm |
| Drawer usable area in G | 20×20 |
| Drawer usable depth | 500 mm |
| Width | 600 mm |
| Base cabinet underneath height-adjustable workstation | no |
| Number of pull-out shelves | 0 |
| Material thickness | 1.2 mm |
| Drawer/pull-out shelf load capacity | 75 kg |

| | |
|--|--|
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 20x20G |
| Type of product | Tool cabinet |

Accessories

| | |
|---|-------------|
| Lock plate for GridLine Type HU21 | 914227 HU21 |
| Drawer, 75 kg Drawer front height 100 mm | 930533 100 |
| Drawer, 75 kg Drawer front height 250 mm | 930533 250 |
| Drawer, 75 kg Drawer front height 75 mm | 930533 75 |
| Drawer, 75 kg Drawer front height 150 mm | 930533 150 |
| Handle end caps 20 pieces Type 10 | 951025 10 |
| Tool cabinet casing for drawers Height 900 mm | 930525 900 |
| Drawer, 75 kg Drawer front height 50 mm | 930533 50 |