

Garant GRIDLINE

## Tool cabinet complete with drawers 75 kg, 26×20G, Height mm / number of drawers: 800/7



### Order data

Order number	930605 800/7
GTIN	4062406065409
Item class	9GK

### Description

#### NOTE: Colour selection possible

#### Version:

Completely equipped tool cabinet in 30×24G, with drawers 26×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

#### Fitted with:

Drawer front height, mm: 50, 50, 75, 75, 100, 150, 200

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 26×20

Height: 800 mm

Width: 750 mm

Depth: 600 mm

Usable height: 700 mm  
 Usable height for drawers: 700 mm  
 Drawer usable width: 650 mm

## Technical description

Height	800 mm
Drawer usable depth	500 mm
Drawer usable depth in G	20
Drawer usable area in G	26×20
Number of drawers	7
Usable height for drawers	700 mm
Drawer usable width	650 mm
Drawer front height	50 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	200 mm
Usable height	700 mm
Width	750 mm
Electronic locking system can be retrofitted	yes
Depth	600 mm
Drawer usable width in G	26
Number of doors	0
Weight	114 kg
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg

Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x20G
Type of product	Tool cabinet

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 800 mm	930625 800
Drawer, 75 kg Drawer front height 100 mm	930633 100
Drawer, 75 kg Drawer front height 150 mm	930633 150
Drawer, 75 kg Drawer front height 200 mm	930633 200
Drawer, 75 kg Drawer front height 50 mm	930633 50
Drawer, 75 kg Drawer front height 75 mm	930633 75
Drawer, 75 kg Drawer front height 125 mm	930633 125
Drawer, 75 kg Drawer front height 300 mm	930633 300
Handle end caps 20 pieces Type 10	951025 10